

toilet

Best way to lift, set & move a toilet!



TK-400





toilet

Operation:

Roll the Toilet Kart to the toilet, 3 clamps attach to the inside of the toilet rim. Once locked against the clamp bar, use the crank to lift the toilet up and hold it stationary above the floor. Roll the toilet where you need it. Fast & easy alignment with closet bolts. Folds to 4 inches wide (see pic on left) for storage or to hang in van...

Made in the USA of powder coated steel tubing.

Dimensions: Height: 40 in. Width: 22 in.* Depth: 18-1/2 in. Weight: 21lbs.

Recommended Load: up to 200+ lbs.

Features:

- For wall mounts, 1 piece, 2 piece: all toilets with a non sloping rim.
- Five minute assembly: attach legs w/clip, reverse crank knob.
- Easily lifts and holds the toilet level until you are ready to install.
- Lifts the rim of the toilet up to 20 inches off the ground.
- Won't drop the toilet.
- Tips back for transport over uneven surfaces.
- *Fits through narrow doors (as small as 19" entry).
- Storage: fold and lock to hang or store. 4" width

Benefits:

- Saves your back = career longevity
- Manpower: multiple toilet setting a 1 person job.
- Cleaner Repair Work don't have to set dirty toilet on the floor.
- Safety: reduces the chance of worker's comp claims.







